

HEDI

Machine / workstation lamp, Type: 10LED



Order data

Order number	081300 10LED
GTIN	4003644000456
Item class	08B

Description

Version:

High quality, universally usable lamps for 250 V / 50 Hz with On / Off switch, 3 m rubber connection cable.

Robust, long, coated flexible metal arm for good mobility of the lamp head and high stability. Machine lamp with **LEDs** for directed illumination of the workplace. Low power consumption, avoids heating up the illuminated objects and subjecting them to UV radiation. Lamp head with improved joint.

Even illumination distribution due to frosted glass cover, beam angle 120°.

Standard:

High quality, universally usable lamps for 250 V / 50 Hz with On / Off switch, 3 m rubber connection cable.

- **Sturdy, long, coated flexible metal arm.**

Supplied with:

Bulb, with **strong magnetic clamp, 50 mm screw-on clamp, and mounting screws** for machine, table, wall or ceiling attachment.

Attention:

German version. Order free UK adapter plug No. 08 1172_GB.

IP Index of Protection: IP 64

Light output: 9.6 W

Illumination: 1100 lm

Number of LEDs: 147
Connection cable length: 3 m
Energy efficiency class : A

Technical description

Energy efficiency class	A
Illumination	1100 lm
Number of LEDs	147
Power supply	Mains-powered
Bulb	LED module
Connection cable length	3 m
Type of fastening	Magnetic foot
Dimmable lighting	no
IP Index of Protection	IP 64
Lamp replaceable	no
Manufacturer's designation	10LED
Light output	9.6 W
Nominal voltage	250 V
Colour temperature	6452 K
Spread angle	120 degrees
ATEX zone	no