



Cordless hammer drill / driver, Type: M18FPD2-5



Order data

Order number	070110 M18FPD2-5
GTIN	4058546222093
Item class	03L

Description

Version:

- **Powerful cordless 2-speed hammer drill / driver with multi-stage torque setting.**
- **REDLITHIUM-ION™ Red Li-ion batteries with single-cell monitoring and charge display.**
- **Sturdy metal gearbox for long working life.**
- **FIXTEC metal quick-change chuck with spindle lock.**
- **Handle with Softgrip coating for comfortable use.**
- **LED illumination of the working area.**
- **Brushless POWERSTATE™-motor (not size M18BPD4) for very high efficiency. Very low wear and up to 10 times the working life of standard DC motors.**
- **REDLINK PLUS™ electronics overload protection and power management.**

FUEL™ with high torque.

Advantage:

Brushless POWERSTATE™ motor.

Supplied with:

Supplied with 2 pcs. Li-ion batteries, charger, transport case (HD box) and belt clip.

Note:

See from No. 073814 and 073840 for suitable batteries and chargers. Suitable Bluetooth tracking module can be found in the online shop.

Packaging: Modular case (HD=Heavy Duty)

suitable battery - supplier / battery type / voltage: Milwaukee type B 18 V

Manufacturer's designation: M18FPD2-502X
 Number of rechargeable batteries contained: 2
 Type of rechargeable battery: Lithium-ion
 Battery capacity: 5 A·h
 Battery voltage: 18 V
 Motor design: FUEL™

Technical description

maximum twist drill size Ø in concrete	16 mm
Battery voltage	18 V
maximum torque	135 N·m
maximum vibration to EN without hammer drill function	1.33 m/s ²
typical application	Heavy Duty
Quick-clamping chuck range	1.5 - 13 mm
Number of rechargeable batteries contained	2
Manufacturer's designation	M18FPD2-502X
Type of rechargeable battery	Lithium-ion
maximum speed 1st speed	0 - 550 min ⁻¹
suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V
maximum twist drill size Ø in wood	89 mm
Battery capacity	5 A·h
maximum speed 2nd speed	2000 min ⁻¹
Motor design	FUEL™
maximum vibration to EN with hammer drill function	13.2 m/s ²
maximum twist drill size Ø in steel	16 mm
Weight	2.2 kg
Packaging	Modular case (HD=Heavy Duty)
Power supply	Rechargeable battery-powered
Suitable for material	Concrete
Suitable for material	Stone
Suitable for material	Masonry

Type of product limpact drill /screwdriver

Accessories

Battery charger Type M1218C 073840 M1218C

Li-ion battery High Output™ Battery type, battery voltage MHB55 V 073809 MHB55

Battery charger Type M1218FC 073840 M1218FC

Li-ion system M18B5 Rechargeable battery type, battery voltage MB18 V 073816 MB18