

Garant GRIDLINE

Vario workbench with 5 drawers and dark grey Eluplan worktop mobile with granite surface plate, Sizes: 1500/5



Order data

Order number	431315 1500/5
GTIN	4062406131821
Item class	41W

Description

Version:

Mobile measurement workstation with granite surface plate. Natural granite surface plate for measuring and inspection, accuracy class 0. Precision diamond lapped for inspection work. Free of flaws; homogeneous structure. Resistant to deflection and to warping. Absolutely rustproof and resistant to acid, low thermal conductivity. **Supplied with M8 tapped hole.**

Worktop of dark Eluplan, 50 mm thick; 2 mm thick plastic surface finish, proof against abrasion and impacts. The coating is anti-static and largely resistant to dilute acids and alkalis. The tough hard surface is particularly suitable for sensitive components. All edges ABS veneered. **Mobile support legs** of square hollow section, each with 2 ball-bearing fixed wheels and castors, Ø 125 mm, with treadless polyurethane tyres. Castors with brakes for the wheels and the castor heads. Back panels and storage shelves of sheet metal. 24G cabinet casing, 600 mm wide, of sheet metal, can be locked centrally with cylinder lock. 100% full extension drawers with differential runners, single-handed individual drawer release system and 75kg load capacity.

Fitted with:

Drawer front height in mm: 50; 75; 75; 100; 125

Supplied with:

Supplied with granite table 630 x 400 mm, accuracy class 0, M8 tapped hole. Fully assembled. Supplied with cabinet casing with drawers.

Colour:

Body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, powder-coated. Suspension for granite table RAL 7016 anthracite, drawer body RAL 7035 light grey (not configurable).

Note:

For accessories see our Workstations and Storage catalogue volume 3.

Technical description

Flatness	0.007 mm
Drawer body height	500 mm
Height	850 mm
Drawer usable depth in G	20
Drawer usable depth	500 mm
maximum load capacity, mobile unit	400 kg
Series	vario
Worktop length	1500 mm
Granite table width	400 mm
Drawer body width	600 mm
Drawer body depth	650 mm
Worktop thickness	50 mm
Granite table length	630 mm
Worktop depth	750 mm
Drawer usable width	500 mm
Weight	208 kg
Drawer usable width in G	20
Design version	Steel hollow section construction
Material thickness	1 mm
Workbench height	850 mm
Drawer/pull-out shelf load capacity	75 kg
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	mobile workbench

