



## Carbide burr Z7 – medium, diamond cut Shank Ø 6 mm, Carbide, Type: D1614



### Order data

Order number	GG5075 D1614
GTIN	4045197730770
Item class	GGN

### Description

#### Version:

**Carbide burrs** with high wear resistance and cutting edge stability. The shank is made of steel if the head Ø is larger than the shank Ø, otherwise it is of carbide. Z7 general-purpose tooth configuration for deburring, edge breaking, cleaning, weld dressing and surface preparation. Suitable for both manual and robot-mounted use.

Shank Ø 6 mm.

same as 540750. **Ball shape** (KUD)

#### Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

#### Content:

**10 burrs / drum.**

#### Note:

**Only sold in bulk pack quantities, not supplied individually. Ordering information: 1 set = 1 drum.**

### Technical description

Toothing grit designation	medium
Overall length	60 mm
Shape description	Ball
Shank Ø	6 mm
Shape	D1614

Tooth type abbreviation	Z7
Type of cut	staggered teeth
Head length L <sub>1</sub>	14 mm
Head Ø	16 mm
Contents	10
Tool material	Carbide
Type of product	Burr

### User data

	Suitability	V <sub>c</sub>	ISO code
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
INOX	suitable only under restricted conditions		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
Uni	suitable		

### Accessories

BurrZ7 – medium, diamond cut Type D1614	540750 D1614
---	--------------