

HOLEX**Carbide burr Z7 – medium, diamond cut Shank Ø 3 mm, Carbide, Type: D0605**

Order data

Order number	GG5691 D0605
GTIN	4045197731036
Item class	GGN

Description

Version:

Carbide burrs with high wear resistance and cutting edge stability. The shank is made of steel if the head Ø is larger than the shank Ø, otherwise it is of carbide. Z7 general-purpose tooth configuration for deburring, edge breaking, cleaning, weld dressing and surface preparation. Suitable for both manual and robot-mounted use.

Carbide mini burrs with shank Ø 3 mm.

same as 546910. **Ball shape** (KUD)

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Content:

10 burrs / drum.

Note:

Only sold in bulk pack quantities, not supplied individually. Ordering information: 1 set = 1 bulk pack.

Technical description

Toothing grit designation	medium
Type of cut	staggered teeth
Shape description	ball
Overall length	38 mm
Head Ø	6.3 mm
Head length L ₁	5 mm
Shape	D0605
Tooth type abbreviation	Z7
Shank Ø	3 mm
Contents	10
Tool material	Carbide
Type of product	Burr

User data

	Suitability	V _c	ISO code
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
INOX	suitable only under restricted conditions		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
Uni	suitable		

Accessories

Mini burrZ7 – medium, diamond cut Type D0605	546910 D0605
--	--------------