

**HOLEX****Carbide burr Z7 – medium, diamond cut Shank Ø 6 mm, Carbide, Type: A1625****Order data**

Order number	GG5075 A1625
GTIN	4045197730626
Item class	GGN

**Description****Version:**

**Carbide burrs** with high wear resistance and cutting edge stability. The shank is made of steel if the head Ø is larger than the shank Ø, otherwise it is of carbide. Z7 general-purpose tooth configuration for deburring, edge breaking, cleaning, weld dressing and surface preparation. Suitable for both manual and robot-mounted use.

Shank Ø 6 mm.  
same as 540750.

**Application:**

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

**Content:**

**10 burrs / drum.**

**Note:**

**Only sold in bulk pack quantities, not supplied individually. Ordering information: 1 set = 1 drum.**

**Technical description**

Toothing grit designation	medium
Head Ø	16 mm
Head length L <sub>1</sub>	25 mm
Overall length	70 mm
Shape	A1625
Shank Ø	6 mm
Type of cut	staggered teeth
Shape description	Cylinder uden endefortanding
Tooth type abbreviation	Z7
Contents	10
Tool material	Carbide
Type of product	Burr

## User data

	Suitability	V <sub>c</sub>	ISO code
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
INOX	suitable only under restricted conditions		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
Uni	suitable		

## Accessories

BurrZ7 – medium, diamond cut Type A1625

540750 A1625