

**HOLEX****Carbide burr Z7 – medium, diamond cut Shank Ø 3 mm, Carbide, Type: A0613****Order data**

Order number	GG5691 A0613
GTIN	4045197730961
Item class	GGN

**Description****Version:**

**Carbide burrs** with high wear resistance and cutting edge stability. The shank is made of steel if the head Ø is larger than the shank Ø, otherwise it is of carbide. Z7 general-purpose tooth configuration for deburring, edge breaking, cleaning, weld dressing and surface preparation. Suitable for both manual and robot-mounted use.

Carbide mini burrs with shank Ø 3 mm.

same as 546910.

**Application:**

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

**Content:**

**10 burrs / drum.**

**Note:**

**Only sold in bulk pack quantities, not supplied individually. Ordering information: 1 set = 1 bulk pack.**

**Technical description**

Type of cut	staggered teeth
Head Ø	6.3 mm
Shank Ø	3 mm
Shape	A0613
Shape description	Cylindrical, without end face cut
Overall length	45 mm
Tooth type abbreviation	Z7
Toothing grit designation	medium
Head length L <sub>1</sub>	12.7 mm
Contents	10
Tool material	Carbide
Type of product	Burr

## User data

	Suitability	V <sub>c</sub>	ISO code
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
INOX	suitable only under restricted conditions		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
Uni	suitable		

## Accessories

Mini burrZ7 – medium, diamond cut Type A0613	546910 A0613
--	--------------