

HOLEX**Carbide burr Z7 – medium, diamond cut Shank Ø 3 mm, Carbide, Type: AS0313****Order data**

Order number	GG5691 AS0313
GTIN	4045197730978
Item class	GGN

Description**Version:**

Carbide burrs with high wear resistance and cutting edge stability. The shank is made of steel if the head Ø is larger than the shank Ø, otherwise it is of carbide. Z7 general-purpose tooth configuration for deburring, edge breaking, cleaning, weld dressing and surface preparation. Suitable for both manual and robot-mounted use.

Carbide mini burrs with shank Ø 3 mm.

same as 546910. **Cylindrical shape (ZYAS), with end cut.**

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Content:

10 burrs / drum.

Note:

Only sold in bulk pack quantities, not supplied individually. Ordering information: 1 set = 1 bulk pack.

Technical description

Shank Ø	3 mm
Head Ø	3 mm
Overall length	38 mm
Shape	AS0613
Head length L ₁	14 mm
Type of cut	staggered teeth
Tooth type abbreviation	Z7
Shape description	Cylindrical with end cut
Toothing grit designation	medium
Contents	10
Tool material	Carbide
Type of product	Burr

User data

	Suitability	V _c	ISO code
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
INOX	suitable only under restricted conditions		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
Uni	suitable		

Accessories

Mini burrZ7 – medium, diamond cut Type AS0313	546910 AS0313
---	---------------