

HOLEX**Carbide burr Z7 – medium, diamond cut Shank Ø 3 mm, Carbide, Type: F0613****Order data**

Order number	GG5691 F0613
GTIN	4045197731074
Item class	GGN

Description**Version:**

Carbide burrs with high wear resistance and cutting edge stability. The shank is made of steel if the head Ø is larger than the shank Ø, otherwise it is of carbide. Z7 general-purpose tooth configuration for deburring, edge breaking, cleaning, weld dressing and surface preparation. Suitable for both manual and robot-mounted use.

Carbide mini burrs with shank Ø 3 mm.

same as 546910. **Round arch shape** (RBF).

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Content:

10 burrs / drum.

Note:

Only sold in bulk pack quantities, not supplied individually. Ordering information: 1 set = 1 bulk pack.

Technical description

Shape	F0613
Tooth type abbreviation	Z7
Head length L ₁	12.7 mm
Shank Ø	3 mm
Shape description	round arch
Overall length	45 mm
Type of cut	staggered teeth
Toothing grit designation	medium
Head Ø	6.4 mm
Contents	10
Tool material	Carbide
Type of product	Burr

User data

	Suitability	V _c	ISO code
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
INOX	suitable only under restricted conditions		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
Uni	suitable		

Accessories

Mini burrZ7 – medium, diamond cut Type F0613	546910 F0613
--	--------------