

**HOLEX****Carbide burr Z7 – medium, diamond cut Shank Ø 6 mm, Carbide, Type: D1210****Order data**

|              |               |
|--------------|---------------|
| Order number | GG5075 D1210  |
| GTIN         | 4045197730763 |
| Item class   | GGN           |

**Description****Version:**

**Carbide burrs** with high wear resistance and cutting edge stability. The shank is made of steel if the head Ø is larger than the shank Ø, otherwise it is of carbide. Z7 general-purpose tooth configuration for deburring, edge breaking, cleaning, weld dressing and surface preparation. Suitable for both manual and robot-mounted use.

Shank Ø 6 mm.

same as 540750. **Ball shape** (KUD)

**Application:**

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

**Content:**

**10 burrs / drum.**

**Note:**

**Only sold in bulk pack quantities, not supplied individually. Ordering information: 1 set = 1 drum.**

**Technical description**

|                            |                 |
|----------------------------|-----------------|
| Shank Ø                    | 6 mm            |
| Shape                      | D1210           |
| Toothing grit designation  | medium          |
| Tooth type abbreviation    | Z7              |
| Head Ø                     | 12 mm           |
| Head length L <sub>1</sub> | 11 mm           |
| Type of cut                | staggered teeth |
| Shape description          | Ball            |
| Overall length             | 56 mm           |
| Contents                   | 10              |
| Tool material              | Carbide         |
| Type of product            | Burr            |

## User data

|                                | Suitability                               | V <sub>c</sub> | ISO code |
|--------------------------------|---|----------------|----------|
| Steel < 900 N/mm <sup>2</sup>  | suitable                                  |                |          |
| Steel < 1400 N/mm <sup>2</sup> | suitable                                  |                |          |
| Steel < 55 HRC                 | suitable                                  |                |          |
| Steel < 60 HRC                 | suitable                                  |                |          |
| INOX                           | suitable only under restricted conditions |                |          |
| Ti                             | suitable only under restricted conditions |                |          |
| GG(G)                          | suitable                                  |                |          |
| Uni                            | suitable                                  |                |          |

## Accessories

|   |              |
|---|--------------|
| BurrZ7 – medium, diamond cut Type D1210 | 540750 D1210 |
|---|--------------|