

HOLEX**Carbide burr Z7 – medium, diamond cut Shank Ø 6 mm, Carbide, Type: E0610****Order data**

Order number	GG5075 E0610
GTIN	4062406201531
Item class	GGN

Description**Version:**

Carbide burrs with high wear resistance and cutting edge stability. The shank is made of steel if the head Ø is larger than the shank Ø, otherwise it is of carbide. Z7 general-purpose tooth configuration for deburring, edge breaking, cleaning, weld dressing and surface preparation. Suitable for both manual and robot-mounted use.

Shank Ø 6 mm.

same as 540750.

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Content:

10 burrs / drum.

Note:

Only sold in bulk pack quantities, not supplied individually. Ordering information: 1 set = 1 drum.

Technical description

Head length L ₁	10 mm
Head Ø	6 mm
Shape description	Teardrop
Shank Ø	6 mm
Overall length	50 mm
Tooth type abbreviation	Z7
Type of cut	staggered teeth
Shape	Teardrop
Toothing grit designation	medium
Contents	10
Tool material	Carbide
Type of product	Burr

User data

	Suitability	V _c	ISO code
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
INOX	suitable only under restricted conditions		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
Uni	suitable		

Accessories

BurrZ7 – medium, diamond cut Type E0610	540750 E0610
---	--------------