



SuperCut Cordless, Type: 7129276SET



Order data

Order number	077805 7129276SET
GTIN	4014586884301
Item class	03F

Description

Version:

Market-leading oscillating tools in three different performance classes (SuperCut, MultiMaster, MultiTalent) in a new version with **Starlock tool arbor** (improved torque transmission of up to 35 % greater rate of progression of the work).

- **Virtually unlimited application possibilities (sawing, grinding, scraping, cutting, rasping) due to the oscillating mode of movement (low generation of dust).**
- **Stepless electronic speed control for optimum working.**
- **Very high quality and stability thanks to the metal gearbox and use of ball bearings and needle bearings throughout.**
- **Optimum handling due to ergonomic design with soft-grip inlays and low weight.**

SuperCut – the highest performance oscillating tool with the highest progression of the work for professional use.

- **Powerful oscillation movement: 2 × 2.0 angular amplitude.**
- **Anti-vibration system with robust motor (housing decoupling).**

Cordless oscillating tool with **brushless EC motor**.

Cordless device of the latest generation with the same performance as mains-powered devices.

Standard:

SuperCut – the highest performance oscillating tool with the highest progression of the work for professional use.

- **Virtually unlimited application possibilities (sawing, grinding, scraping, cutting, rasping) due to the oscillating mode of movement (low generation of dust).**
- **Stepless electronic speed control for optimum working.**

- **Very high quality and stability thanks to the metal gearbox and use of ball bearings and needle bearings throughout.**
- **Optimum handling due to ergonomic design with soft-grip inlays and low weight.**

Supplied with:

Charger, carrying case.

Note:

See No. 073835 ff and 073845 for suitable spare batteries and chargers.

suitable battery - supplier / battery type / voltage: Fein type E 18 V

Manufacturer's designation: AFSC 18 QSL

Battery capacity: 6 Ah

Battery voltage: 18 V

Toolholder: StarlockMax, StarlockPlus, Starlock

Speed of oscillation: 10000 - 19500 rpm

Angle of oscillation: 4 degrees

Technical description

Manufacturer's designation	AFSC 18 QSL
Weight	1.8 kg
Battery voltage	18 V
Speed of oscillation	10000 - 19500 rpm
Battery capacity	6 Ah
Toolholder	StarlockMax, StarlockPlus, Starlock
Width across grinding plate head	80 mm
Type of rechargeable battery	Lithium-ion
Number of rechargeable batteries contained	2
Angle of oscillation	4 degrees
Power supply	Rechargeable battery-powered
Packaging	Carrying case
suitable battery - supplier / battery type / voltage	Fein type E 18 V
Type of product	Oscillator

Accessories

Li-ion battery Battery type, battery voltage FE18 V	073834 FE18
Li-ion battery Rechargeable battery type, battery voltage FE18 V	073835 FE18
Li-ion battery Rechargeable battery type, battery voltage FE18 V	073837 FE18
Li-ion battery Battery type, battery voltage FE18 V	073838 FE18
Li-ion battery Battery type, battery voltage FE18_E V	073838 FE18_E
Battery charger Type FE80	073845 FE80