

Garant

Circular saw blade, metal, alternating teeth with bevel universal, Blade Ø D: 136mm

**Order data**

Order number	584095 136
GTIN	4062406133511
Item class	51S

Description**Version:**

Tipped with carbide inserts, precision version with high-strength blade, noise damped. Generously dimensioned carbide teeth allow multiple re-grinding. **With mounting hole Ø 20 mm.**

Application:

For circular, cross-cut, compound, and mitre saws.

Universal circular saw blade for cutting **a wide range of materials** such as **steel flats and angle sections**, aluminium and other non-ferrous metals. Flat teeth with bevel up to Ø 250 mm; alternating set with bevel from Ø 300 mm.

Note:

Further circular saw blades can be found in Group 17.

Technical description

Bore Ø	20 mm
Number of teeth	30

Width of cut B	1.6 mm
Type of product	Circular saw blade