



## Tapper up to M10, Type: 71090162



### Order data

Order number	075550 71090162
GTIN	4014586885537
Item class	03F

### Description

#### Version:

- **Electronic speed control for responsive starting.**
- **Sustained power for reliable performance.**
- **Integral reversing gear and quick backing out.**
- **FEIN sensitive handle for non-fatiguing and safe working.**
- **Integral switch for ease of use.**

18 V **battery** tap up to M 10.

#### Supplied with:

**Without drill chuck.** With additional handle. A collet chuck (No. 075580 size 063012) or a jaw chuck (No. 075580 size 019009) is required for operation. **Without battery.** Supplied with plastic tool case.

#### Note:

Suitable rechargeable battery starter set No. 073832.

Packaging: Carrying case

suitable battery - supplier / battery type / voltage: Fein type E 18 V

Manufacturer's designation: AGWP 10 Select

maximum speed: 0 - 440 min<sup>-1</sup>

Toolholder: B12

maximum machine tap Ø in steel: M10

Weight: 1.6 kg

maximum vibration to EN: < 2.5 m/s<sup>2</sup>

## Technical description

maximum speed	0 - 440 min <sup>-1</sup>
maximum vibration to EN	< 2.5 m/s <sup>2</sup>
maximum machine tap Ø in steel	M10
Toolholder	B12
Weight	1.6 kg
Manufacturer's designation	AGWP 10 Select
suitable battery - supplier / battery type / voltage	Fein type E 18 V
Power supply	Rechargeable battery-powered
Packaging	Carrying case
Type of product	Tap driver

## Accessories

Thread tapping accessories Type 009013	075580 009013
Thread tapping accessories Type 063012	075580 063012
Li-ion battery Rechargeable battery type, battery voltage FE18 V	073835 FE18
Li-ion battery HighPower Battery type, battery voltage FE18 V	073834 FE18
Battery starter set Type 9260430701	073832 9260430701
Battery starter set Type 9260431401	073832 9260431401
Thread tapping accessories Type 019009	075580 019009