



## Lamp magnifier varioLED+, Lens Ø: 132mm



### Order data

Order number	491655 132
GTIN	4048347905806
Item class	49A

### Description

#### Version:

- Ergonomic design - low power consumption - long-life LEDs (up to 50,000 operating hours).
- Lamp magnifier with 84 long-life high-power LEDs.
- Adjustable ring illumination or segmented illumination, dimmable in 3 stages. Strength of illumination ring illumination: 6000 lx/ 3500 lx/ 2400 lx; segmented illumination: 2350 lx/ 1450lx/ 960 lx.
- Colour temperature 6500 K.
- Ra value 86.
- Full light output immediately - flicker-free.
- PXM® aspherical lightweight lens with cera-tec® hard coating and 3.55 dpt/2× and Ø 132 mm permits a wide field of view, image is sharp right to the edges and free from distortion, for non-fatiguing work.
- Lens cover can be swung aside or removed.
- Quick change of view between magnification and normal view using "free-swinging" lens.
- Extremely low weight and 6 joints allow optimum alignment of the magnification head for any situation – variety of fastening options.

#### Supplied with:

Table clamp for worktop thicknesses 18 – 74 mm.

**Optional extras:**

Additional lens 6 dpt/2.5× magnification with Ø 132 mm.

**Note:**

Table base and lens spray protection for the underside are available on request.

The light source can be exchanged by the manufacturer.

---

**Technical description**

Magnification (x-times)	1.9
Lens Ø	132 mm
Length of the jointed arm A	400 mm
Length of the jointed arm B	400 mm
Power supply	Mains operated
Type of product	Magnifying glass lamp