



Indexable milling cutter 90° MFWN, with bore, Ø D / number of teeth Z: 50/4mm



Order data

Order number	225615 50/4
GTIN	2050001929945
Item class	250

Description

Version:

Milling cutter with double-sided indexable inserts.

The combination of approach angle, chip chamber design as well as the geometries and cutting angles of the indexable inserts ensure outstanding metal removal rates, chip clearance, working life, and low cutting forces, and hence high cost-effectiveness.

Technical description

Cutting edge Ø D _c	50 mm
suitable indexable insert	WNMU 0806..
maximum cutting depth a _{p max}	8 mm
Mounting bore Ø	22 mm
Insert screw	229700 (T15; 4.2 Nm)
Overall length L _{tot}	40 mm
Number of cutting edges Z	4

Shank type	with bore
Setting angle κ	90 degrees
Milling application	End milling
Milling application	Plunging
Through-coolant	yes
Type of product	End / face mill

Accessories

Clamping screw	229700
----------------	--------