


Solid carbide milling cutter HPC, TiSi, Ø f8 DC: 3mm

Order data

Order number	GG1014 3
GTIN	4045197735560
Item class	GGN

Description

Version:
Special TiSi coating.
Same as No. 203014.

Technical description

Recess $\varnothing D_1$	2.8 mm
Feed f_z for side milling in INOX > 900 N/mm ²	0.015 mm
No. of teeth Z	4
Flute length L_c	8 mm
Shank	DIN 6535 HB to h6
Tolerance nominal \varnothing	f8
Corner chamfer width at 45°	0.1 mm
Overhang length L_1 incl. recess	13 mm
Direction of infeed	horizontal, oblique and vertical
Shank $\varnothing D_s$	6 mm

Cutting edge $\varnothing D_c$	3 mm
Feed f_z for slot milling in stainless steel $> 900 \text{ N/mm}^2$	0.012 mm
Overall length L	57 mm
Helix angle	35 degrees
Contents	5
Coating	TiSi
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	N
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Cutting width a_e for milling operation	$0.3 \times D$ for side milling
Cutting width a_e for milling operation	Full slot cutting depth $1 \times D$
Machining strategy	HPC
Colour ring	blue
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Steel $< 500 \text{ N/mm}^2$	suitable	240 m/min	P
Steel $< 750 \text{ N/mm}^2$	suitable	220 m/min	P
Steel $< 900 \text{ N/mm}^2$	suitable	180 m/min	P
Steel $< 1100 \text{ N/mm}^2$	suitable	180 m/min	P
Steel $< 1400 \text{ N/mm}^2$	suitable	150 m/min	P
TOOLOX 33	suitable	115 m/min	H
TOOLOX 44	suitable	80 m/min	H
INOX $< 900 \text{ N/mm}^2$	suitable	90 m/min	M
INOX $> 900 \text{ N/mm}^2$	suitable	80 m/min	M

Uni	suitable only under restricted conditions
wet maximum	suitable
wet minimum	suitable only under restricted conditions
dry	suitable
Air	suitable

Accessories

Solid carbide milling cutterHPC Ø f8 DC 3 mm

203014 3