

HOLEX**HOLEX Pro Steel Solid carbide roughing end mill HPC, TiAlN, Ø DC: 3mm****Order data**

Order number	GG1054 3
GTIN	4045197735768
Item class	GGN

Description**Version:**

For **roughing and finishing**.

Up to $1 \times D$ into solid material **at very high feed rates** with smooth cutting action. Dimensions to **manufacturer's standard**.

Same as No. 203054.

Advantage:

Optimised flute form, eccentric relief ground, wide chip space.

Content:

5 pieces.

Technical description

Flute length L_c	8 mm
Tolerance nominal \varnothing	0 / -0.03
Feed f_z for side milling in steel $< 900 \text{ N/mm}^2$	0.025 mm
Overall length L	57 mm
Overhang length L_1 incl. recess	12 mm
No. of teeth Z	4

Cutting edge $\varnothing D_c$	3 mm
Feed f_z for slot milling in steel < 900 N/mm ²	0.02 mm
Direction of infeed	horizontal, oblique and vertical
Shank	DIN 6535 HB to h6
Shank $\varnothing D_s$	6 mm
Corner chamfer width at 45°	0.13 mm
Recess $\varnothing D_1$	2.8 mm
Helix angle	38 degrees
Contents	5
Series	Pro Steel
Coating	TiAlN
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	N
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Cutting width a_e for milling operation	0.3×D for side milling
Cutting width a_e for milling operation	Full slot cutting depth 1×D
Machining strategy	HPC
Colour ring	green
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Steel < 500 N/mm ²	suitable	260 m/min	P
Steel < 750 N/mm ²	suitable	240 m/min	P
Steel < 900 N/mm ²	suitable	180 m/min	P
Steel < 1100 N/mm ²	suitable	160 m/min	P

INOX < 900 N/mm ²	suitable only under restricted conditions	80 m/min	M
GG(G)	suitable	250 m/min	K
Uni	suitable		
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		
dry	suitable		
Air	suitable		

Accessories

HOLEX Pro Steel solid carbide roughing end millHPC Ø DC
3 mm

203054 3