



## Solid carbide roughing end mill HPC, TiAlN, Ø d11 DC: 8mm



### Order data

Order number	GG1491 8
GTIN	4045197735911
Item class	GGN

### Description

#### Version:

With knuckle profile for roughing.

Very high rate of metal removal.

Can be used as universal roughing end mill.

Without dynamic twist pitch.

Size **16M MID mills: Dimensions to manufacturer's standard.**

**Same as No. 205492.**

### Technical description

Feed $f_z$ for slot milling in steel < 900 N/mm <sup>2</sup>	0.04 mm
Cutting edge Ø $D_c$	8 mm
Corner chamfer width at 45°	0.3 mm
Feed $f_z$ for side milling in steel < 900 N/mm <sup>2</sup>	0.045 mm
No. of teeth Z	4
Shank Ø $D_s$	8 mm
Shank	DIN 6535 HB to h6

Overall length L	63 mm
Direction of infeed	horizontal, oblique and vertical
Flute length $L_c$	16 mm
Tolerance nominal $\varnothing$	d11
Helix angle	30 degrees
Contents	5
Coating	TiAlN
Tool material	Solid carbide
Standard	DIN 6527
Milling profile	HR
Cutting width $a_e$ for milling operation	0.5×D for side milling
Cutting width $a_e$ for milling operation	Full slot cutting depth 1×D
Machining strategy	HPC
Colour ring	without
Type of product	End / face mill

## User data

	Suitability	$V_c$	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	270 m/min	N
Alu > 10% Si	suitable only under restricted conditions	190 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	115 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	100 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	95 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	65 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable	55 m/min	P
INOX > 900 N/mm <sup>2</sup>	suitable only under restricted conditions	55 m/min	M
GG(G)	suitable	85 m/min	K

Uni	suitable only under restricted conditions
wet maximum	suitable
wet minimum	suitable only under restricted conditions
dry	suitable only under restricted conditions
Air	suitable

---

## Accessories

Solid carbide roughing end millHPC Ø d11 DC 8 mm	205492 8
--	----------