

Mitutoyo

Digital external micrometer with data output, Measuring range: 75-105mm



Order data

Order number	421590 75-105
GTIN	4946368736723
Item class	44A

Description

Version:

Error limits more accurate than the requirements of **DIN 863. On / Off, Origin (basic setting), Zero / Abs** (for zeroing in any position), **Hold / Data** (save measurement value or send data).

Description:

- **Spindle pitch 10 mm per revolution reduces the approach time.**
- **Non-rotating spindle protects the surfaces being measured.**
- **Absolute measuring system. No need to set zero point after switching on. Prevents measurement errors.**

Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

1 battery No. 081560 size 357. 1 micrometer standard from size 25-55.

Optional extras:

Data cable No. 497445.

Technical description

Measuring range	75 - 105 mm
Spindle pitch	10 mm
Spindle Ø	6.35 mm
Calibration	B2

Scale divisions	0.001 mm
Error limit	3 µm
Article no of the battery / rechargeable battery fitted	081560 357
Series	QuickMike
Number of batteries contained	1
IP Index of Protection	IP 65
Power supply	Battery-powered
Standard	Manufacturer's standard
Reversible reading	mm / inch
Interface	USB interface
Interface	Digimatic interface
Measured value saving	once-off setting of the zero position
Measurement technology	digital
Packaging	sturdy box
Type of product	External tube micrometer

Services

Calibration External micrometer including setting dimension maximum measuring range 200 mm	022040 200
DAkkS calibration External micrometer including setting dimension maximum measuring range 200 mm	022050 200

Accessories

Button cell / special battery Battery type 357	081560 357
Connecting cable with data switch Type USB2	497445 USB2
Connecting cable with data switch Type D1	497445 D1
Connecting cable with data switch Type D2	497445 D2