

Garant
Tool24 Smartline – cabinet system including dividing material, Type: S54

Order data

Order number	979001 S54
GTIN	4062406133931
Item class	9SA

Description
Version:

Flexible industrial vending solution for storage and management of machining and assembly tools, measuring tools, protective workwear and many other consumable items. The master system can be extended and combined with additional extension systems of any Tool24 hardware variants. The individual software packages allow the systems to be tailored to your exact requirements.

Body and doors made of 1 mm sheet metal. Pallet truck base made of 1.75 mm sheet metal. Storage shelf made of bamboo.

Application:

Automatic industrial vending solution for storage and management of tools and C-items.

Content:

Dividers: 200 pcs. No. 960540 size 149; 12 pcs. No. 960560 size 149

Fitted with:

Number of drawers × drawer front height: 48×50 mm; 6×100 mm

Supplied with:

Extension systems: tool issuing cabinet with dividers.

Colour:

Body RAL 7035 light grey, drawers RAL 7016 anthracite **powder-coated**.

Technical description

Width	717 mm
Height	1390 mm
Depth	750 mm
Number of drawers	54
Type	Extension cabinet complete
Weight	404 kg
Drawer/pull-out shelf load capacity	15 kg
Drawer usable width	153 mm
Storage area	5 m ²
Division within a drawer	9×36 U
Drawer usable depth	612 mm
Series	Tool24 Smartline
Drawer runner extension	Anti-tilt lock
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Tool issuing system