

Garant**Tool24 Locker – master system DE, Type: 180/40****Order data**

Order number	979300 180/40
GTIN	4062406134754
Item class	9SA

Description**Version:**

Goods issuing system with compartments of different sizes to ensure secure and complete documentation of individual withdrawals. The compartment sizes permit storage of larger items and are prepared for charging of batteries. LED interior lighting available as standard both assists identification and withdrawal of items in the compartments that open automatically, even in dark environments. The LED strip along the compartments assists both insertion and withdrawal. Perforated panels fitted to both ends permit the flexible attachment of a touch monitor for master variants. Easyfix hooks and brackets together with all other perforated panel accessories listed in our catalogue can be fitted.

The master system can be extended and combined with additional extension systems of any Tool24 hardware variants.

This article is compatible with the Hoffmann Group Connected software solutions. Individual issuing system with 40 compartments for smaller items.

Advantage:**Hoffmann Group Connected**

With this article you are gaining a building block for your digitally networked production. Increased productivity can be achieved together with the respective software module.

Application:

Automatic individual issuing system also for storage and management of bulky items such as large PPE, power tools, hand tools and our L-BOXX® modular plastic boxes.

Fitted with:

Number of compartments × height in mm: 32 × 140; 8 × 220

Supplied with:

Master system DE with 22 inch touch screen, barcode scanner, PC including basic software package.

Colour:

Body RAL 7035 light grey, fronts RAL 7016 anthracite grey, **powder-coated.**

Note:

All compartments are pre-configured for provision of a power supply via the technical duct. The connection of individual chargers must be arranged by the customer. The weight values in the technical data are for the extension system cabinets themselves, without PC and display screen. Compartments with viewing windows, individual colours and dimensions (compartment sizes, cabinet widths and depths) are optionally available.

Please speak to your specialist adviser!

Technical description

Height	1965 mm
Weight	275 kg
Depth	500 mm
Width	1100 mm
Number of compartments	40
Load capacity per compartment	25 kg
Usable depth of compartment	450 mm
Usable height of the compartment (1)	140 mm
Usable height of the compartment (2)	220 mm
Usable width of the compartment	180 mm
Series	Tool24 Locker
Series	Hoffmann Group Connected
Series	Tool24 Locker
Interface	Hoffmann Group Connected
Hoffmann perforated panel grid interval	9×9 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003

Type of product

Tool issuing system