



## Universal hole saw without centre drill, Hole Ø: 30mm



### Order data

|              |               |
|--------------|---------------|
| Order number | 788041 30     |
| GTIN         | 4058546228675 |
| Item class   | 76G           |

### Description

#### Version:

Carbide teeth for a longer working life, even when drilling into dense materials. Wide and deep flutes for easy removal of the drilled core. Aggressive tooth geometry for up to 10x quicker drill progression in comparison to bi-metal hole saws. Ideal for use in the electronics area and installation area.

#### Application:

For drilling larger holes and breaking throughs in various materials: masonry, lightweight materials, plastics, and wood. Unsuitable for use in hard materials such as concrete, granite, natural stone and hard tiles with a hardness greater than 30 N/mm<sup>2</sup>.

#### Note:

**Use only with rotary drive (no impact).**

### Technical description

|                                  |   |
|----------------------------------|---|
| Number of cutting edges Z        | 2   |
| maximum cutting depth            | 60 mm                                       |
| For use on                       | Sanitation and heating pipes, halogen lamps |
| Use with impact / without impact | not for impact drilling                     |
| Tool material                    | Carbide                                     |
| Type of product                  | Hole saw                                    |

---

## Accessories

Special adapter with centre drill overall length 115-6KT mm

788052 115-6KT