

**XF 733 fibre disc (CER), Ø 125 mm, Grit: 80****Order data**

Order number	566452 80
GTIN	4018875876008
Item class	56V

**Description****Version:**

Tear-resistant but very flexible **vulcanised fibre**. Bore diameter 22.23 mm and crossed slots. **VSM XF 733** with **maximum grinding performance and working life** on non-ferrous metals, such as **aluminium**. The active grinding layer prevents clogging and adhesion of sawdust. Grit type: **Ceramic grit with abrasion-active coating (STEARAT Plus)**.

**Application:**

Limited to maximum 80 m/s circumferential speed with backing pads No. 566650 / 6670 on angle grinders. For **grinding flat and curved surfaces** with a high degree of **flexibility**.

**Technical description**

Grit	80
Disc Ø	125 mm
Series	XF733
Grinding media	Ceramic grit
Grinding medium code	Ceramic

Iron, sulphur and chlorine constituents	< 0.1 %
Product name attribute	Ø 125 mm
Bore Ø	22.23 mm
optimised for material	Aluminium
maximum circumferential speed	80 m/s
Type of product	Fibre disc

### User data

	Suitability	V <sub>c</sub>	ISO code
Alu Mg	suitable		
CuZn	suitable		
dry	suitable		