



Cordless sabre saw, Type: M18FSX-12



Order data

Order number	078220 M18FSX-12
GTIN	4058546224295
Item class	03L

Description

Version:

Milwaukee cordless sabre saw for working in difficult-to-access areas.

- **Electronic controls with steplessly variable stroke length and overload protection.**
- **Tool-less FIXTEC saw blade quick-release clamping system.**

Supplied with:

Supplied with HD box carrying case, 1 pcs. 18 V / 12 Ah High Output batteries, quick charger and sabre saw blade.

Note:

Sabre saw blades can be found from No. 588600.

See No. 073810; 073811; 073814; 073815; 073816; 073829 for suitable spare batteries and chargers.

Technical description

Battery capacity	12 Ah
Weight	5.5 kg
suitable battery - supplier / battery type / voltage	Milwaukee type HB 18 V

Rate of strokes	0 - 3000 min ⁻¹
Stroke length	28.6 mm
maximum vibration to EN	22.2 m/s ²
Battery voltage	18 V
Packaging	Modular case (HD=Heavy Duty)
Special features	FIXTEC, LED
Manufacturer's designation	M18FSX-121C
Number of rechargeable batteries contained	1
Type of rechargeable battery	Lithium-ion
Power supply	Rechargeable battery-powered
Type of product	Saw

Accessories

Li-ion battery High Output™ Battery type MHB12	073811 MHB12
--	--------------