



Cordless impact wrench 18V



Order data

Order number	074010 M18ONEFF-1
GTIN	4058546029050
Item class	03L

Description

Version:

Robust and **powerful FUEL™ cordless impact wrench** with **brushless POWERSTATE™ EC motor**, for long motor service life and high energy efficiency. Sturdy **metal gearbox casing** and ergonomic **central handle with soft-grip coating**. Stage of charge display, LED illumination of the working area. Reversible, with electronic speed control. **REDLINK PLUS™ electronics** – for unique power management:

- **With system communication between the drive machine and battery.**
- **With overload protection for longer working life of the battery, motor, and gearbox.**

DRIVE CONTROL™ permits quick switching between the 4 available settings with different speeds and torques. The first **1 inch 18-V cordless impact wrench in the world FUEL™** delivers up to 2033 Nm torque from a compact tool, and needs neither a cable nor compressed air to do it. Integral impact rate adjustment increases the reproducible results for the chosen torque setting. With new **High-Output™ 8.0 Ah** battery.

- **ONE KEY™ app for individualising the tool settings.**
- **ONE KEY™ tool tracker & security permits amongst other things a display of the latest position of the device.**

Version of the advertising text:

Robust and **powerful FUEL™ cordless impact screwdriver** with **brushless POWERSTATE™ EC motor** for long motor service life and high energy efficiency.

Advantage:

DRIVE CONTROL™.

Supplied with:

Supplied with 2× Li-ion batteries, charger, HD box, belt clip.

Note:

For matching spare batteries and accessories see from No. 073808.

Technical description

maximum torque 1st step	530 Nm
Tool arbor size	1 in
Number of impacts 4th setting	0 - 2500 min ⁻¹
Battery voltage	18 V
Manufacturer's designation	M18ONEFHIWF1-802X
Number of impacts 3rd stage	0 - 2100 min ⁻¹
Number of impacts 2nd stage	0 - 1650 min ⁻¹
suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V
suitable battery - supplier / battery type / voltage	Milwaukee type HB 18 V
App link	OneKey
maximum torque 4th setting	2033 Nm
Number of impacts 1st stage	0 - 1350 min ⁻¹
typical application	Heavy Duty
Tool arbor drive profile	External square drive
maximum screw Ø (8.8 - 12.9)	M42
maximum torque 2nd step	1020 Nm
maximum torque 3rd step	1800 Nm
Weight	5.9 kg
Battery capacity	8 Ah
Packaging	Modular case (HD=Heavy Duty)
Number of rechargeable batteries contained	2
Type of rechargeable battery	Lithium-ion
Power supply	Rechargeable battery-powered

Suitable for material	Steel
Type of product	Impact wrench

Accessories

Li-ion batteryHigh Output™ Battery type MHB8	073810 MHB8
Battery starter setHigh Output™ Type M18HNRG8	073831 M18HNRG8