


**Solid carbide drill plain shank DIN 6535 HE, TiAlN, Ø DC m7 (mm or inch): 4,9**

**Order data**

Order number	122773 4,9
GTIN	4062406150488
Item class	12F

**Description**
**Version:**

Tool specially matched to drilling holes without through-coolant. **Concave major cutting edges** and a **special flute profile** ensure a good chip evacuation. The sturdy cutter geometry with **special point geometry** and 4 cutting edges ensures drilling with good process reliability. A wide range of applications in steel materials thanks to a combination of tough ultra-fine grain carbide and extremely **wear-resistant** and **heat-resistant coating**.

**Note:**

Flute length  $L_c = L_2 + 1.5 \times D_c$ .

Through-coolant: no

Standard: DIN 6537

Tolerance nominal Ø: m7

Number of cutting edges Z: 2

recommended maximum drilling depth  $L_2$ : 36.65 mm

Tolerance nominal Ø: m7

Overall length L: 82 mm

Shank Ø  $D_s$ : 6 mm

Feed f in steel < 900 N/mm<sup>2</sup>: 0.16 mm/rev.

**Technical description**

recommended maximum drilling depth $L_2$	36.65 mm
Flute length $L_c$	44 mm
Standard	DIN 6537
Tolerance nominal Ø	m7
Shank Ø $D_s$	6 mm

Number of cutting edges Z	2
Feed f in steel < 900 N/mm <sup>2</sup>	0.16 mm/rev.
Overall length L	82 mm
Nominal Ø D <sub>c</sub>	4.9 mm
Coating	TiAlN
Tool material	Solid carbide
Version	6×D
Point angle	140°
Shank	DIN 6535 HE to h6
Through-coolant	no
Colour ring	green
Type of product	Jobber drill

## User data

	Suitability	V <sub>c</sub>	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	200 m/min	N
Alu > 10% Si	suitable only under restricted conditions	160 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	110 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	90 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	80 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	70 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable only under restricted conditions	60 m/min	P
GG	suitable	90 m/min	K
GGG	suitable only under restricted conditions	60 m/min	K
Uni	suitable		
wet maximum	suitable		

dry

suitable only under  
restricted conditions