

JEPSON POWER**Metal cutting hand-held circular saw, Type: 8230****Order data**

Order number	078234 8230
GTIN	4260052466834
Item class	07E

Description**Version:**

Powerful metal cutting cold circular saws for sawing sheet metal, sandwich panels, metal plates, tubes and sections of steel, non-ferrous metals, and composite materials **without generating sparks.**

- **No need to use cooling lubricants.**
- **No reworking necessary.**
- **Cuts in seconds.**

Metal cutting **hand-held circular saw.**

- **Precise blade guidance, low burr formation.**
- **Sturdy stop plate.**

Metal cutting **hand-held circular saw.**

- **Mobile – solid and lightweight – only 7.1 kg.**
- **Ideal for sawing sheet metal, sandwich panels, stainless steel, metal plates, pipes and profiles made from steel, non-ferrous materials and composite materials, up to a thickness of 10 mm.**

Supplied with:

Supplied with 1 × saw blade 48Z No. 078239 size 48 and carrying case.

Note:

Slides for 078234 available on request:
Slide 1400 mm for size 8320

Slide 600-1200mm for size 8230.

Metal cutting circular saw DRY MITER Cutter 9410ND for delicate sawing in soft and delicate material available on request.

Technical description

Saw blade Ø	230 mm
maximum cutting depth 90°	84 mm
maximum cutting depth 45°	56 mm
maximum speed	2600 min ⁻¹
Mains frequency	50 Hz
Manufacturer's designation	8230
Weight	7.1 kg
Power consumption	1700 W
AC supply voltage	230 V
Power supply	Mains operated
Packaging	Transport case
Type of product	Saw

Accessories

Drytec® carbide circular saw blade Ø 230×25.4 mm Number of teeth 48	078239 48
Stand for No. 078231 Type 600526	078238 600526
Drytec® carbide circular saw blade Ø 230×25.4 mm Number of teeth 84	078239 84
Drytec® carbide circular saw blade Ø 230×25.4 mm Number of teeth 60	078239 60