

Garant
Solid carbide NC machine reamer, TiAlN, Nominal Ø DC: 15mm

Order data

Order number	164341 15
GTIN	4062406136819
Item class	11P

Description
Version:

Version suitable for NC similar to DIN 8093 **with straight shank Ø** for **standard chucking** especially in **hydraulic chucks** or **high precision collet chucks**. This ensures **the highest concentricity**.

Tolerance specifications:

Size 0.6 – 0.9: Manufacturing or cutting edge tolerance **0/+0.004 mm**.

Size 0.98 – 20: Reamer manufacturing or cutting edge tolerance to DIN1420 for **H7 bore tolerance**.

No need to procure special collets when using GARANT-NC reamers. With long flutes and left-hand helix.

Application:

For reaming through holes, as the chips are evacuated in the cutting direction. Lead taper is suitable also for blind holes.

Note:

For reamers like No. 164340 and 164341 but with other diameters and fits see No. 164344 and 164345.

Technical description

Tolerance	H7
Shank Ø D _s	16 mm
Feed f in steel < 1100 N/mm ²	0.18 mm/rev.
Nominal Ø D _c	15 mm
Overhang L ₁	110 mm
Number of cutting edges Z	8

Overall length L	162 mm
Flute length L _c	50 mm
Reaming oversize in diameter	0.2 - 0.3 mm
Coating	TiAlN
Tool material	Solid carbide
Standard	Manufacturer's standard
Through-coolant	no
Shank	DIN 6535 HA with h6
Application for type of drilling	for through holes
Colour ring	green
Type of product	Phillips bit

User data

	Suitability	V _c	ISO code
Aluminium	suitable	35 m/min	N
Aluminium (short chipping)	suitable	30 m/min	N
Alu > 10% Si	suitable only under restricted conditions	25 m/min	N
Steel < 500 N/mm ²	suitable	30 m/min	P
Steel < 750 N/mm ²	suitable	25 m/min	P
Steel < 900 N/mm ²	suitable	20 m/min	P
Steel < 1100 N/mm ²	suitable	15 m/min	P
Steel < 1400 N/mm ²	suitable	10 m/min	P
INOX < 900 N/mm ²	suitable	15 m/min	M
INOX > 900 N/mm ²	suitable	12 m/min	M
Ti > 850 N/mm ²	suitable only under restricted conditions	10 m/min	S
GG(G)	suitable	10 m/min	K
CuZn	suitable	25 m/min	N

Uni	suitable
wet maximum	suitable