



GWX angle grinder, Type: 9-115S



Order data

Order number	077050 9-115S
GTIN	3165140962537
Item class	03C

Description

Version:

- **Quick and easy:** Easy change of angle grinder accessories without any parts that could be lost or need for additional tools.
- **No additional wrenches required.**
- **Comprehensive:** Huge range of angle grinders and accessories with complete backwards compatibility.
- **Maximum convenience due to 100% quick tool exchange requiring no tools.**
- **Reliable:** Directional accessories can no longer be mounted incorrectly thanks to the innovative X-LOCK system. Very high user protection thanks to the acoustic signal when fitting is correct.
- **Clean working without annoying scratches! Less prominent and fewer scuffs with X-LOCK angle grinders.**

115-mm angle grinder, 900 W motor with direct cooling. **X-Lock system.**

Supplied with:

Supplied with additional vibration control handle, safety hood, craftsman's case.

Technical description

Speed range	2800 - 11000 min ⁻¹
Power consumption	900 W
Restart block	yes
Special features	Variable speed

Manufacturer's designation	GWX 9-115 S
maximum disc Ø	115 mm
Weight	2.1 kg
Packaging	Modular case (L-Boxx)
Power supply	Mains operated
Series	X-LOCK system
Type of product	Angle grinder