



Core drilling machine, Type: MABASIC200



Order data

Order number	076535 MABASIC200
GTIN	4250187506604
Item class	07E

Description

Version:

- **Integral internal lubrication system, magnetic indicator for monitoring the magnetic clamping force.**
- **Integral cutting oil container, complete cable routing within the casing.**
- **Oil bath gearbox.**

Single-speed magnetic core drilling machine for drill \varnothing up to 32 mm. With 19 mm (3/4 inch) Weldon arbor.

Supplied with:

Carrying case, core drill holder, ejector pin for core drills, safety chain, lubrication system, and operating tools.

Note:

- **See No. 118780 to 118825 for core drills.**
- **Core drilling machines with automatic feed, vacuum clamping plate and pipe clamping fixtures available on request.**
- **Pneumatic core drilling machines with ATEX standard available on request.**

Technical description

Weight	12 kg
Power consumption	900 W
Width of the magnetic base	168 mm
maximum twist drill size Ø in steel	13 mm
Length	260 mm
maximum speed 1st speed	450 min ⁻¹
Height	360 mm
Working stroke	160 mm
Manufacturer's designation	MABASIC200
maximum core drill Ø in steel	32 mm
Width	160 mm
Length of magnetic base	84 mm
Tool arbor size	19 mm Weldon
Power supply	Mains operated
Packaging	Carrying case
Type of product	Core drilling machine

Accessories

Carbide core drillDepth of cut 30 mm Ø DC 15 mm	118780 15
Carbide core drillDepth of cut 30 mm Ø DC 22 mm	118780 22
Carbide core drillDepth of cut 30 mm Ø DC 16 mm	118780 16
Carbide core drillDepth of cut 30 mm Ø DC 20 mm	118780 20
Carbide core drillDepth of cut 30 mm Ø DC 17 mm	118780 17
Carbide core drillDepth of cut 30 mm Ø DC 18 mm	118780 18
Carbide core drillDepth of cut 30 mm Ø DC 26 mm	118780 26
Carbide core drillDepth of cut 30 mm Ø DC 21 mm	118780 21
HSS core drill set	118825
Carbide core drillDepth of cut 30 mm Ø DC 25 mm	118780 25

Carbide core drillDepth of cut 30 mm Ø DC 14 mm	118780 14
Carbide core drillDepth of cut 30 mm Ø DC 24 mm	118780 24
Carbide core drillDepth of cut 30 mm Ø DC 23 mm	118780 23
Carbide core drillDepth of cut 30 mm Ø DC 19 mm	118780 19