



Carbide-tipped hammer drill, SDS-max, Ø×overall length: 40X920mm



Order data

Order number	789204 40X920
GTIN	3165140565868
Item class	76K

Description

Version:

Special carbide insert geometry for longer tool lives.

TARGET TIP TECHNOLOGY – more severely angled tip: More precise drilling, no slipping on the surface, aggressive drilling in concrete steel and faster drilling speed. PGM-certified – approves precise drilled holes suitable for plugs, both for chemical and mechanical anchors. Large flute channels for quick evacuation of waste material, resulting in less friction.

Drill head with square cross section from Ø 16 mm.

Application:

For drilling concrete, natural stone, and masonry.

Note:

Generation SDS-max-7 with embedded carbide cutters, soldered.

Technical description

overall length	920 mm
Ø	40 mm
Flute length	800 mm
Tool material	Carbide
Use with impact / without impact	Impact drilling
Shank	SDS Max
Type of product	Masonry drill

