

HOLEX**Three-jaw lathe chuck cast-iron with recessed mount, DIN 702-4, External Ø A: 125mm****Order data**

Order number

312906 125

GTIN

4062406154516

Item class

32W

Description**Version:**

- **Manual chucks with gear scroll, centrally clamping.**
- **Body made of cast iron or steel.**
- **Gear scroll drop-forged, balanced, and hardened.**
- **Flanks of scroll and of jaw serrations are ground.**
- **High concentricity, more precise than DIN 6386 requirement.**

Application:

For machine spindles with recessed centring mount or for mounting using a flange. The chuck is secured from the rear by means of screws. The flange blanks must always be fitted first to the machine and then to the chuck.

Standard:**DIN 702-4.****Supplied with:**

Includes: 1 set = 3 hardened inside jaws, stepped on the outside.

1 set = 3 hardened outside jaws, stepped on the inside.

1 clamping wrench and fastening screws or studs depending on the chuck.

Optional extras:

Spare and additional jaws No. 312971 – 312986.

Technical description

Centring depth C	4 mm
External Ø A	125 mm
Weight	5 kg
Aperture E	32 mm
Centring Ø B	95 mm
maximum speed	4000 min ⁻¹
Height with jaws H ₂	76 mm
Height without jaws H ₁	56 mm
Standard	DIN 702-4
Material	Cast iron
Colour code for accessories	HOLEX geared scroll chucks and jaws
Type of product	Gear scroll chucks

Accessories

Workpiece back-stop, base module Height h 15 mm	313036 15
Base jaw set, 3 pieces, hardened for chuck type 125	312976 125
Scroll jaw set, 3 pieces, soft for chuck type 125	312971 125
Workpiece backstop Height h 15 mm	313033 15
Top jaw set 3-piece, soft for chuck type 125	312980 125
Top jaw set, 3 pieces, soft for chuck type 125	312981 125
Inside jaw set, 3 pieces, hardened for chuck type 125	312986 125