

HOLEX

Three-jaw lathe chuck cast-iron with recessed mount, DIN 702-4, External Ø A: 200mm



Order data

Order number

312906 200

GTIN

4062406154530

Item class

32W

Description

Version:

- **Manual chucks with gear scroll, centrally clamping.**
- **Body made of cast iron or steel.**
- **Gear scroll drop-forged, balanced, and hardened.**
- **Flanks of scroll and of jaw serrations are ground.**
- **High concentricity, more precise than DIN 6386 requirement.**

Application:

For machine spindles with recessed centring mount or for mounting using a flange. The chuck is secured from the rear by means of screws. The flange blanks must always be fitted first to the machine and then to the chuck.

Standard:

DIN 702-4.

Supplied with:

Includes: 1 set = 3 hardened inside jaws, stepped on the outside.

1 set = 3 hardened outside jaws, stepped on the inside.

1 clamping wrench and fastening screws or studs depending on the chuck.

Optional extras:

Spare and additional jaws No. 312971 – 312986.

Technical description

Aperture E	55 mm
Weight	17.5 kg
maximum speed	3000 min ⁻¹
Centring Ø B	160 mm
External Ø A	200 mm
Centring depth C	4 mm
Height with jaws H ₂	104 mm
Height without jaws H ₁	75 mm
Standard	DIN 702-4
Material	Cast iron
Colour code for accessories	HOLEX geared scroll chucks and jaws
Type of product	Gear scroll chucks

Accessories

Base jaw set, 3 pieces, hardened for chuck type 200	312976 200
Top jaw set, 3 pieces, soft for chuck type 200	312981 200
Workpiece backstop Height h 15 mm	313033 15
Workpiece back-stop, base module Height h 15 mm	313036 15
Inside jaw set, 3 pieces, hardened for chuck type 200	312986 200
Scroll jaw set 3 pieces, soft for chuck type 200	312970 200
Scroll jaw set, 3 pieces, soft for chuck type 200	312971 200