



## Three-jaw lathe chuck steel short taper mount, DIN 702-3, Outer Ø A / taper: 160/5mm



### Order data

Order number	312931 160/5
GTIN	4062406154783
Item class	32W

### Description

#### Version:

- **Manual chucks with gear scroll, centrally clamping.**
- **Body made of cast iron or steel.**
- **Gear scroll drop-forged, balanced, and hardened.**
- **Flanks of scroll and of jaw serrations are ground.**
- **High concentricity.**

#### Application:

**The chuck is always fitted to the spindle nose directly without an intermediate flange.**

For spindle noses DIN 55027 with **studs and collar nuts.**

#### Standard:

**DIN 702-3.**

#### Supplied with:

Includes: 1 set = 3 hardened inside jaws, stepped on the outside.

1 set = 3 hardened outside jaws, stepped on the inside.

1 clamping wrench and fastening screws or studs depending on the chuck.

#### Optional extras:

**Spare and additional jaws** No. 312971 – 312986.

## Technical description

Height with jaws H <sub>2</sub>	100 mm
Height without jaws H <sub>1</sub>	68 mm
External Ø A	160 mm
Weight	9 kg
Aperture E	42 mm
maximum speed	4600 min <sup>-1</sup>
Taper size	5
Centring Ø B	82.5 mm
Standard	DIN 702-3
Colour code for accessories	HOLEX geared scroll chucks and jaws
Type of product	Gear scroll chucks

---

## Accessories

Workpiece backstop Height h 15 mm	313033 15
Workpiece back-stop, base module Height h 15 mm	313036 15