



High feed rate milling cutter MFH mini, Plain shank, $\varnothing D$ / number of teeth Z: 17/2 mm



Order data

Order number	221950 17/2
GTIN	4960664741236
Item class	250

Description

High feed rate milling cutter MFH mini 17/2 mm Through-coolant: yes

Number of cutting edges Z: 2

$\varnothing D_3$: 10 mm

maximum cutting depth $a_{p\max}$: 1 mm

Overhang L_1 : 20 mm

Overall length L_{tot} : 100 mm

Shank $\varnothing D_s$ h6: 16 mm

Technical description

Cutting edge $\varnothing D_c$	17 mm
Overhang L_1	20 mm
$\varnothing D_3$	10 mm
Shank $\varnothing D_s$ h6	16 mm
maximum cutting depth $a_{p\max}$	1 mm
Overall length L_{tot}	100 mm
suitable indexable insert	LOGU 0303..
Insert screw	229713 (8IP; 1.2 Nm)
Number of cutting edges Z	2
Through-coolant	yes

Circular interpolation milling $\varnothing D_{\max}$	32 mm
Circular interpolation milling $\varnothing D_{\min}$	27 mm
Ramping angle α_{\max}	2.07 °
Ramping length L for α_{\max}	8.3 mm
Setting angle κ	15 °
Shank type	Plain shank
Milling application	Circular milling
Milling application	Ramping
Milling application	Plunging
Machining strategy	HPC

Accessories

Clamping screw	229713
----------------	--------