



High feed rate milling cutter MFH mini, Plain shank, $\varnothing D$ / number of teeth Z: 32/5mm



Order data

Order number	221950 32/5
GTIN	4960664741335
Item class	250

Technical description

Insert screw	229713 (8IP; 1.2 Nm)
Overhang L_1	70 mm
maximum cutting depth $a_{p\max}$	1 mm
$\varnothing D_3$	25 mm
suitable indexable insert	LOGU 0303..
Shank $\varnothing D_s$ h6	32 mm
Overall length L_{tot}	150 mm
Cutting edge $\varnothing D_c$	32 mm
Number of cutting edges Z	5
Through-coolant	yes
Circular interpolation milling $\varnothing D_{\max}$	62 mm
Circular interpolation milling $\varnothing D_{\min}$	57 mm
Ramping angle α_{\max}	0.74 degrees
Ramping length L for α_{\max}	23.3 mm
Setting angle κ	15 degrees
Shank type	Plain shank

Milling application	Circular milling
Milling application	Ramping
Milling application	Plunging
Machining strategy	HPC
Type of product	Copy mill

Accessories

Clamping screw	229713
----------------	--------