

Garant**Abrasive sponge pack, 24 pieces extra soft, 120×98×13 mm, Grit: 60****Order data**

Order number	557480 60
GTIN	4062406155971
Item class	51E

Description**Version:**

Grinding sponge with **extra soft** intermediate layer. An outstanding fit to all profiles. **Coated on 2 sides.**

Aluminium oxide (A) with a **ceramic coating** for a **longer working life.**

Reduced alien material penetration into the workpiece surface by a bonding structure free of solvents.

Advantage:

- **Resilient, no formation of kinks or folds.**
- **All sponges also suitable for wet grinding.**
- **Low tendency to clog, can be washed out.**

Application:

For **finish smoothing of irregularities and profiled surfaces** without changing the geometry. Grinding metal, wood and plastics before painting, or between coats of paint, to provide a key.

Technical description

Grit	60
Grit designation	medium
Grinding media	Standard aluminium oxide (A)
Grinding medium code	A

Width	98 mm
Height	13 mm
Length	120 mm
Product name attribute	120×98×13 mm
Number of coated surfaces	2
Number of sponges, pads	24
Type of product	Abrasive sanding sponge

User data

	Suitability	V _c	ISO code
Alu Mg	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable only under restricted conditions		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
Stone	suitable only under restricted conditions		
Paint	suitable		
Uni	suitable		
wet maximum	suitable		
dry	suitable		

