

**Garant****Abrasive block pack, 24 pieces hard, 100×68×26 mm, Grit: 60****Order data**

|              |               |
|--------------|---------------|
| Order number | 557470 60     |
| GTIN         | 4062406155933 |
| Item class   | 51E           |

**Description****Version:**

**Abrasive block** in **hard** version, with increased edge stability. **Coated on 4 sides** with aluminium oxide grit (A).

**Ceramic coating** for a **longer working life**.

Reduced ingress of foreign material into the workpiece surface by a bonding structure free of solvents.

**Advantage:**

- **Resilient, no formation of kinks or folds.**
- **All sponges also suitable for wet grinding.**
- **Low tendency to clog, can be washed out.**

**Application:**

For deburring and surface sanding of wood, metal and paintwork.

**Technical description**

|                      |                              |
|----------------------|------------------------------|
| Grit                 | 60                           |
| Grit designation     | medium                       |
| Grinding media       | Standard aluminium oxide (A) |
| Grinding medium code | A                            |
| Width                | 68 mm                        |

|                           |                         |
|---------------------------|-------------------------|
| Height                    | 26 mm                   |
| Length                    | 100 mm                  |
| Product name attribute    | 100×68×26 mm            |
| Number of coated surfaces | 4                       |
| Number of sponges, pads   | 24                      |
| Type of product           | Abrasive sanding sponge |

### User data

|                                | Suitability                               | V <sub>c</sub> | ISO code |
|--------------------------------|---|----------------|----------|
| Alu Mg                         | suitable                                  |                |          |
| Steel < 900 N/mm <sup>2</sup>  | suitable                                  |                |          |
| Steel < 1400 N/mm <sup>2</sup> | suitable                                  |                |          |
| Steel < 55 HRC                 | suitable                                  |                |          |
| Steel < 60 HRC                 | suitable                                  |                |          |
| Steel < 67 HRC                 | suitable only under restricted conditions |                |          |
| INOX                           | suitable                                  |                |          |
| Ti                             | suitable                                  |                |          |
| GG(G)                          | suitable                                  |                |          |
| CuZn                           | suitable                                  |                |          |
| Plastic, GRP                   | suitable                                  |                |          |
| Wood                           | suitable                                  |                |          |
| Stone                          | suitable only under restricted conditions |                |          |
| Paint                          | suitable                                  |                |          |
| Uni                            | suitable                                  |                |          |
| wet maximum                    | suitable                                  |                |          |
| dry                            | suitable                                  |                |          |

