



## High feed rate milling cutter MFH mini, with thread, $\varnothing D$ / number of teeth Z: 28/5mm



### Order data

Order number	221960 28/5
GTIN	
Item class	250

### Description

#### Technical description

Insert screw	229713 (8IP; 1.2 Nm)
Overall length $L_{tot}$	35 mm
Mounting thread M	M12
$\varnothing D_3$	21 mm
suitable indexable insert	LOGU 0303..
Cutting edge $\varnothing D_c$	28 mm
Number of cutting edges Z	5
maximum cutting depth $a_{p,max}$	1 mm
Through-coolant	yes
Ramping length L for $\alpha_{max}$	19.3 mm
Circular interpolation milling $\varnothing D_{min}$	49 mm
Ramping angle $\alpha_{max}$	0.89°
Circular interpolation milling $\varnothing D_{max}$	54 mm

Shank type	with thread
Milling application	Circular milling
Milling application	Ramping
Milling application	Plunging
Machining strategy	HPC
Type of product	Copy mill

---

## Accessories

Clamping screw	229713
----------------	--------