

Garant**Abrasive block pack, 24 pieces hard, 100×68×26 mm, Grit: 150****Order data**

Order number	557470 150
GTIN	4062406155957
Item class	51E

Description**Version:**

Abrasive block in **hard** version, with increased edge stability. **Coated on 4 sides** with aluminium oxide grit (A).

Ceramic coating for a **longer working life**.

Reduced ingress of foreign material into the workpiece surface by a bonding structure free of solvents.

Advantage:

- **Resilient, no formation of kinks or folds.**
- **All sponges also suitable for wet grinding.**
- **Low tendency to clog, can be washed out.**

Application:

For deburring and surface sanding of wood, metal and paintwork.

Technical description

Grit	150
Grit designation	very fine
Grinding media	Standard aluminium oxide (A)
Grinding medium code	A
Width	68 mm

Height	26 mm
Length	100 mm
Product name attribute	100×68×26 mm
Number of coated surfaces	4
Number of sponges, pads	24
Type of product	Abrasive sanding sponge

User data

	Suitability	V _c	ISO code
Alu Mg	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable only under restricted conditions		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
Stone	suitable only under restricted conditions		
Paint	suitable		
Uni	suitable		
wet maximum	suitable		
dry	suitable		

