



## High feed rate milling cutter MFH mini, Weldon shank, $\varnothing D$ / number of teeth Z: 16/2mm



### Order data

Order number	221955 16/2
GTIN	4960664741359
Item class	250

### Technical description

Overall length $L_{tot}$	79 mm
Insert screw	229713 (8IP; 1.2 Nm)
Cutting edge $\varnothing D_c$	16 mm
maximum cutting depth $a_{p,max}$	1 mm
suitable indexable insert	LOGU 0303..
Overhang $L_1$	30 mm
Shank $\varnothing D_s$ h6	16 mm
Number of cutting edges Z	2
$\varnothing D_3$	9 mm
Through-coolant	yes
Circular interpolation milling $\varnothing D_{max}$	30 mm
Circular interpolation milling $\varnothing D_{min}$	25 mm
Ramping angle $\alpha_{max}$	2.35 degrees
Ramping length L for $\alpha_{max}$	7.3 mm
Setting angle $\kappa$	15 degrees
Shank type	Weldon shank

Milling application	Circular milling
Milling application	Plunging
Milling application	Ramping
Machining strategy	HPC
Type of product	Copy mill

---

## Accessories

Clamping screw	229713
----------------	--------