

Garant
Hammer set, Number of tools: 3

Order data

Order number	954665 3
GTIN	2050002004375
Item class	91A

Description
Version:

Popular tool sets in two-colour moulded PE rigid foam inlays. The closed-pore foam is oil-resistant and does not absorb liquids of any sort. Upper layer anthracite, under which the contrast colour of blue indicates if a tool is missing.

The rigid foam inlays fill 1/4 (10 G × 8 G or 250 × 200 mm) or 1/2 (20 G × 8 G or 500 × 200 mm) of the usable drawer area.

Suitable for :

New GARANT roller cabinets with full extension drawers and a new drawer module of **20 G × 16 G** or 500 × 400 mm (W × D).

Supplied with:

Rigid foam inlay, empty No. 952001 size 954665: 1 pc.

GARANT engineer's hammer No. 750110 size 300; 500: 1 pc. each

GARANT dead-blow plastic hammer No. 754750 size 40: 1 pc.

Degree of fill of a drawer in units: 8×20

Width: 200 mm

Depth: 500 mm

Width in G: 8

Depth in G: 20

Technical description

Width in G	8
Width	200 mm

Depth in G	20
Number of tools	3
Depth	500 mm
Rigid foam quality LD45, thickness	30 mm
Degree of fill of a drawer in units	8x20
Type of product	Rigid foam inlay

Accessories

Engineer's hammer with handle protection collar Weight without handle 500 g	750110 500
Engineer's hammer with handle protection collar Weight without handle 300 g	750110 300
Dead-blow hammer with nylon inserts Hickory handle Hammer head Ø 40 mm	754750 40
Rigid foam inlay for tool sets suitable for rigid foam set 954665	952001 954665
Dead-blow hammer with steel tube handle Hammer head Ø 40 mm	754900 40