



## High feed rate milling cutter MFH mini, with thread, $\varnothing D$ / number of teeth Z: 16/2mm



### Order data

Order number	221960 16/2
GTIN	4960664741038
Item class	250

### Technical description

Mounting thread M	M8
$\varnothing D_3$	9 mm
Overall length $L_{tot}$	25 mm
Number of cutting edges Z	2
maximum cutting depth $a_{p\ max}$	1 mm
suitable indexable insert	LOGU 0303..
Cutting edge $\varnothing D_c$	16 mm
Insert screw	229713 (8IP; 1.2 Nm)
Through-coolant	yes
Ramping length L for $\alpha_{max}$	7.3 mm
Circular interpolation milling $\varnothing D_{min}$	25 mm
Ramping angle $\alpha_{max}$	2.35 degrees
Circular interpolation milling $\varnothing D_{max}$	30 mm
Shank type	with thread
Milling application	Circular milling

Milling application	Ramping
Milling application	Plunging
Machining strategy	HPC
Type of product	Copy mill

---

## Accessories

Clamping screw	229713
----------------	--------