

Chisel, taper pin punch, pin punch set, Number of tools: 10



Order data

Order number	954678 10
GTIN	2050002004382
Item class	91A

Description

Version:

Popular tool sets in two-colour moulded PE rigid foam inlays. The closed-pore foam is oil-resistant and does not absorb liquids of any sort. **Upper layer anthracite**, under which the **contrast colour** of blue indicates if a tool is missing.

The rigid foam inlays fill 1/4 (10 G × 10 G or 250 × 250 mm) or 1/2 (10 G × 20 G or 250 × 500 mm) of the usable drawer area.

Suitable for:

New GARANT GridLine workbenches with full extension drawers and a new drawer module of 20 G × 20 G or 500 × 500 mm (W × D).

Supplied with:

Rigid foam inlay, empty No. 952001 size 954678: 1 pc.

Flat cold chisel No. 740500 size 200: 1 pc.

Cross-cut chisel No. 740600 size 200: 1 pc.

Taper pin punch No. 745500 size 3; 4: 1 pc. each

Pin punch No. 747000 size 2; 3; 4; 5; 6; 8: 1 pc. each

Technical description

Width	250 mm
-------	--------

Depth in G	10
Number of tools	10
Depth	250 mm
Width in G	10
Version	with striking tool
Weight	1.344 kg
Rigid foam quality LD45, thickness	30 mm
Degree of fill of a drawer in units	10×10
Type of product	Rigid foam inlay

Accessories

Pin punch, standard quality, painted Point Ø D 2 mm	747000 2
Taper pin punch heavy version Tip Ø 4 mm	745500 4
Rigid foam inlay for tool sets suitable for rigid foam set 954678	952001 954678
Pin punch, standard quality, painted Point Ø D 5 mm	747000 5
Pin punch, standard quality, painted Point Ø D 4 mm	747000 4
Pin punch, standard quality, painted Point Ø D 6 mm	747000 6
Taper pin punch heavy version Tip Ø 3 mm	745500 3
Pin punch, standard quality, painted Point Ø D 8 mm	747000 8
Flat chisel overall length 200 mm	740500 200
Cross-cut chisel overall length 200 mm	740600 200
Pin punch, standard quality, painted Point Ø D 3 mm	747000 3