



High feed rate milling cutter MFH mini, with thread, Ø D / number of teeth Z: 17/2 mm

Order data

Order number	221960 17/2
GTIN	4960664741045
Item class	250

Description

High feed rate milling cutter MFH mini 17/2 mm Through-coolant: true
 Number of cutting edges Z: 2
 Ø D₃: 9 mm
 maximum cutting depth a_{p max}: 1 mm
 Overall length L_{tot}: 25 mm
 Mounting thread M: M8
 suitable indexable insert: LOGU 0303..

Technical description

Tool exchange	
Shank type	with thread
Direction of infeed	
Machining strategy	HPC
Milling application	Circular milling
Milling application	Ramping
Milling application	Plunging
Milling head suitable for insert shape	
Spacing of the cutters	
Setting angle κ	
Type of product	

