



Abrasive flap disc speed ZA, flat, Ø 178 mm, Grit: 60



Order data

Order number	565296 60
GTIN	4062406159665
Item class	52M

Description

Version:

- High-quality zirconium aluminium oxide (ZA) for high abrasive performance.
- Glass fibre pad for optimum contact pressure.
- Suitable for both steel and stainless steel.
- Best results on angle grinders of all power classes.

speed - flat flap strip arrangement, for **high metal removal rate** and long tool life.

Application:

Precise chamfering, edge smoothing and surface abrasion.

Technical description

Disc Ø	178 mm
Bore Ø	22.23 mm
Shape description	flat
Grinding media	Zirconium abrasive (ZA)
Grinding medium code	ZA

Iron, sulphur and chlorine constituents	< 0.1 %
Product name attribute	Ø 178 mm
optimised for material	INOX
optimised for material	Steel
maximum circumferential speed	80 m/s
Type of product	Abrasive flap disc

User data

	Suitability	V _c	ISO code
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable only under restricted conditions		
GG(G)	suitable only under restricted conditions		
Uni	suitable		
dry	suitable		