



High feed rate milling cutter MFH mini, with thread, $\varnothing D$ / number of teeth Z: 25/4mm



Order data

Order number	221960 25/4
GTIN	4960664741106
Item class	250

Technical description

Mounting thread M	M12
Overall length L_{tot}	35 mm
maximum cutting depth $a_{p\ max}$	1 mm
$\varnothing D_3$	18 mm
Number of cutting edges Z	4
suitable indexable insert	LOGU 0303..
Insert screw	229713 (8IP; 1.2 Nm)
Cutting edge $\varnothing D_c$	25 mm
Through-coolant	yes
Ramping length L for α_{max}	16.3 mm
Circular interpolation milling $\varnothing D_{min}$	43 mm
Ramping angle α_{max}	1.05 degrees
Circular interpolation milling $\varnothing D_{max}$	48 mm
Shank type	with thread
Milling application	Circular milling

Milling application	Ramping
Milling application	Plunging
Machining strategy	HPC
Type of product	Copy mill

Accessories

Clamping screw	229713
----------------	--------