


Garant
CNC video measuring microscope MM1, Type: 300CMZ

Order data

Order number	492550 300CMZ
GTIN	4062406160272
Item class	41P

Description
Version:

CNC-controlled video measuring microscope with quicker image processing, high-resolution colour camera, and a multi-touch panel based on a PC, easy to operate, suitable for the workshop environment.

Incident light: 56 white LEDs in 2 concentric rings. 1 ring and 4 segments can each be separately switched and dimmed.

Transillumination: Long-life LEDs, telecentric, can be switched and dimmed. **Solid granite base** with surface-hardened indexing table and high-precision guides.

- **Easy installation and use of measurement programmes.**
- **Practical automation of measuring processes, for example pallet measurements.**
- **Modern user-friendly measurement software for intuitive operation.**

With motorised zoom lens, magnification from 0.3x to 3.5 and coaxial light for uniform illumination of components.

Supplied with:

All-in-One PC, wireless mouse and keyboard, dust cover, power supply unit, test certificate, and multi-lingual user manual.

Optional extras:

Lens No. 491912, software option No. 491913, cutting edge cleaner No. 354788.

Note:

Length measurement variation $E_{UXY, MPE}$ according to DIN EN ISO 10360-7, measured with magnification factor = 0.5.

Permissible ambient conditions: $20\text{ °C} \pm 1\text{ K}$, temperature gradient $\Delta_{th} = 0.5\text{ K/h}$, $\Delta_{td} = 4.0\text{ K/d}$, measured with a calibrated standard.

We reserve the right to make technical changes and to change the touch panel version.

Technical description

Height	950 mm
Measuring range Z	200 mm
maximum component weight	20 kg
Length measurement variation $E_{UXY, MPE}$ optically (2D)	$2.9 + L / 100$ (L in mm) at $20\text{ °C} \pm 1\text{ K}$ μm
Lens (times)	0.3 – 3.5
Working distance	80 mm
Width	900 mm
Measuring range X	300 mm
maximum component height	200 mm
Magnification at the screen (times)	10 - 162
Camera	6.4 megapixels, autofocus
Weight	115 kg
Measuring range Y	200 mm
Field of view	$24 \times 16 - 2 \times 1\text{ mm}$
Length	730 mm
Nominal voltage	240 V
Power supply	Mains operated
Type of product	CNC video measuring microscope

Accessories

Accessories for video measuring microscopes Type FEDER	491917 FEDER
--	--------------

Software option for MM1 Type PROFIL	491913 PROFIL
Base cabinet for measuring microscopes width×depth 1800X900 mm	491914 1800X900
Dust cover Type 300	491919 300
Lens for measuring microscopes MM1/MM2 Type 3	491912 3
Software option for MM1 Type DXF	491913 DXF
Spare glass plate for video measuring microscope MM1 Type 300	491948 300