


**CC.T 09T302, Grade: CA515**

**Order data**

Order number	260096 CA515
GTIN	4960664674909
Item class	25E

**Description**

CC.T 09T302 CA515 Grade: CA515

Chip breaker: HQ

Tolerance: M

Cutting depth  $a_p$ : 0.5 - 2.5 mm

Feed  $f$ : 0.05 - 0.25 mm/rev.

Cutting speed  $v_c$  main application: 110 - 380 m/min

**Technical description**

Cutting depth $a_p$	0.5 - 2.5 mm
Cutting speed $v_c$ main application	110 - 380 m/min
Chip breaker	HQ
Feed $f$	0.05 - 0.25 mm/rev.
Main application	P
Corner radius	0.2 mm
Cutting conditions	continuous

Grade	CA515
Finishing/roughing assignment	Finishing
Tool material	Carbide
ISO code indexable insert	CCMT 09T302
Number of changes/inserts	2
Tolerance	M
Type of product	Indexable insert for turning